



Linear Position Transmitter HLT 2150-R1

Magnetostrictive

For partial integration

Resolution 0.1 mm

Analogue

Description:

The HLT 2150 is a linear position transmitter which, due to its compact design, was developed in particular for use in applications where space is very limited. A wide range of accessories such as magnets is available for individual adaptation to the particular application.

The HLT 2150 is suited for measuring ranges up to 2.5 m.

The different output signals (analogue current / voltage) enable connection to all HYDAC ELECTRONIC GmbH measurement and control devices as well as connection to standard evaluation systems (e.g. to PLC controls).

The main fields of application for the HLT 2150 are, for example, general positioning tasks in mechanical engineering and in mobile and stationary hydraulics, as a partially integrated solution in hydraulic cylinders.

Technical data:

Input data

Measuring ranges	50 .. 2500 mm
Model	Rod with M18x1.5 screw-in flange acc. to ISO 6149 Operating pressure: ≤ 450 bar Peak pressure acc. to DIN EN ISO 19879: 630 bar
Tightening torque, recommended	50 Nm
Material	Rod: Stainless steel 1.4571 Housing: Stainless steel 1.4301

Output data

Output signal, permitted load resistance	Current:	4 .. 20 mA or 20 .. 4 mA Load resist.: 200 .. 500 Ω
	Voltage:	0 .. 10 V or 10 .. 0 V 0.25 .. 4.75 V or 4.75 .. 0.25 V 0.5 .. 9.5 V 0.5 .. 4.5 V Load resist.: min 2 kΩ

Resolution	12 bit, ≥ 0.1 mm
Non-linearity	≤ ± 0.05 % FS
Hysteresis	≤ ± 0.1 % FS
Repeatability	≤ ± 0.1 % FS
Temperature coefficient	≤ ± 0.01 % FS / °C
Sampling rate	2 ms

Environmental conditions

Operating temperature range	-40 .. +85 °C
Storage temperature range	-40 .. +100 °C
Fluid temperature range	-40 .. +120 °C
CE mark	EN 61000-6-1 / 2 / 3 / 4

Vibration resistance acc. to DIN EN 60068-2-6 at 10 .. 500 Hz at 5 kHz	≤ 20 g ≤ 15 g
--	------------------

Shock resistance acc. to DIN EN 60068-2-27 (11 ms)	≤ 50 g
---	--------

Protection class acc. to DIN EN 60529 ¹⁾	IP 67
---	-------

Installation position	No restrictions
-----------------------	-----------------

Other data


Supply voltage	9 .. 30 V DC
Residual ripple of supply voltage	≤ 250 mV _{pp}
Current consumption without output	< 100 mA
Weight	Depending on length: 50 mm: ~ 400 g 2500 mm: ~ 1100 g

Note: Reverse polarity protection of the supply voltage, overvoltage and short circuit protection are provided.

FS (Full Scale) = relative to complete measuring range


¹⁾ With mounted mating connector in corresponding protection class

Dimensions:



Pin connections:

M12x1, 4 pole



Pin

1	+U _B
2	n.c.
3	0 V
4	Signal

Model code:

HLT 2 1 5 0 - R1 - 006 - XXX - XXXX - 000

Design / geometry type

1 = rod

Model

R1 = rod with M18x1.5 screw-in flange

Electrical connection

006 = male M12x1, 4 pole

Output signal

C01 = analogue 4 .. 20 mA, 3-conductor

C02 = analogue 20 .. 4 mA, 3-conductor

B01 = analogue 0 .. 10 V

B02 = analogue 10 .. 0 V

G01 = analogue 0.25 .. 4.75 V

G02 = analogue 4.75 .. 0.25 V

G03 = analogue 0.5 .. 9.5 V

G04 = analogue 0.5 .. 4.5 V

Measuring range in mm (50 .. 2500 mm)

Example

O150 = 150 mm

Modification

000 = standard

Notes:

The position magnet must be ordered separately.

Scope of delivery:

- HLT 2150
- Operating manual

Accessories available: (not supplied with instrument)

ZBL MR17.4	position magnet	part no.: 6119372
ZBL MR22	position magnet	part no.: 6084453
ZBL MR33	position magnet	part no.: 6084207
ZBL MV63	position magnet	part no.: 6084454
Intermediate ring	AD33xID13.5x5	part no.: 3887829

More detailed information on accessories as well as on further accessories, such as mating connectors, can be found in the Accessories brochure.

Note:

The information in this brochure relates to the operating conditions and applications described.

For applications or operating conditions not described, please contact the relevant technical department.

Subject to technical modifications.

HYDAC ELECTRONIC GMBH

Hauptstraße 27, 66128 Saarbrücken

Germany

Telephone +49 (0)6897 509-01

Fax +49 (0)6897 509-1726

E-mail: electronic@hydac.com

Internet: www.hydac.com