



## Pressure Switch EDS 410 for series applications

Relative pressure

Factory-set

Customised designs thanks to diverse electrical and mechanical connections  
Up to 2 switching outputs

### Description:

The electronic pressure switch EDS 410 has been specially developed for use in series applications, and is based on the EDS 4000 pressure switch series.

The EDS 410 is available with one or two transistor outputs (PNP), which can be defined as either N/C or N/O.

The switch and switch-back points of the EDS 410 are factory-set acc. to customer specification (not field-adjustable). As with the EDS 4000 standard model, the EDS 410 has a ceramic measurement cell with thick-layer strain gauge for measuring relative pressure in the low pressure range, and a measurement cell with thin-film strain gauge on a stainless steel membrane for measuring in the high pressure range.

Various pressure ranges between 0 .. 1 bar and 0 .. 600 bar as well as different electrical and mechanical connection types are available.

### Technical data:

#### Input data

Measuring ranges	bar	1	2.5	6	10	16	40	60	100	250	400	600
Overload pressures	bar	3	8	18	30	48	80	120	200	500	800	1000
Burst pressure	bar	5	12	30	50	80	180	300	500	1250	2000	2000
Mechanical connection <sup>1)</sup>	G1/4 A ISO 1179-2											
Tightening torque, recommended	20 Nm											
Parts in contact with fluid	Mech. connection: Stainless steel Sensor cell: Ceramic or stainless steel Seal: FKM or EPDM (as per model code)											

#### Output data

Switching outputs	1 or 2 transistor outputs PNP or NPN Switching current: PNP: max. 1.2 A with 1 switching output max. 1 A each with 2 switching outputs NPN: max. 0.5 A with 1 switching output max. 0.3 A each with 2 switching outputs Switching cycles: > 100 million Switch points/switch-back points: acc. to customer specification Switch-on and switch-off delay: 8 .. 2000 ms (standard 32 ms); factory-set acc. to customer specification
Accuracy acc. to DIN 16086, terminal based	≤ ± 0.5 % FS typ. ≤ ± 1 % FS max.
Temperature compensation, zero point	≤ ± 0.02 % FS / °C typ. ≤ ± 0.03 % FS / °C max.
Temperature compensation, span	≤ ± 0.02 % FS / °C typ. ≤ ± 0.03 % FS / °C max.
Repeatability	≤ 0.1 % FS max.
Long-term drift	≤ ± 0.3 % FS typ. / year

#### Environmental conditions

Compensated temperature range	-25 .. +85 °C
Operating temperature range <sup>2)</sup>	-40 .. +85 °C / -25 .. +85 °C
Storage temperature range	-40 .. +100 °C
Fluid temperature range <sup>2)</sup>	-40 .. +100 °C / -25 .. +100 °C
CE mark	EN 61000-6-1 / 2 / 3 / 4
Vibration resistance acc. to DIN EN 60068-2-6 at 10 .. 500 Hz	≤ 20 g
Shock resistance acc. to DIN EN 60068-2-27 (1 ms)	≤ 100 g
Protection class acc. to DIN EN 60529 <sup>3)</sup>	IP 65 IP 67

#### Other data

Electrical connection <sup>1)</sup>	e.g. EN175301-803 M12x1 (4 pole) jacketed cable
Supply voltage	8 .. 42 V DC
Residual ripple of supply voltage	≤ 5 %
Current consumption	≤ 25 mA with inactive switching outputs ≤ 1.225 A with 1 switching output ≤ 2.425 A with 2 switching outputs
Weight	~ 145 g

Note: Reverse polarity protection of the supply voltage, overvoltage, override and short circuit protection are provided.


**FS (Full Scale)** = relative to complete measuring range

<sup>1)</sup> Additional connection options available on request

<sup>2)</sup> -25 °C with FKM or EPDM seal, -40 °C on request

<sup>3)</sup> With mounted mating connector in corresponding protection class

## Dimensions:



## Note:

The information in this brochure relates to the operating conditions and applications described.

For applications or operating conditions not described, please contact the relevant technical department.

Subject to technical modifications.

## Order details:

The electronic pressure switch EDS 410 has been specially developed for OEM customers and is available for minimum order quantities of 50 pieces per type.

For precise specifications, please contact the Sales Department of HYDAC ELECTRONIC.

**HYDAC ELECTRONIC GMBH**  
 Hauptstr. 27, 66128 Saarbrücken  
 Germany  
 Telephone +49 (0)6897 509-01  
 Fax +49 (0)6897 509-1726  
 e-mail: [electronic@hydac.com](mailto:electronic@hydac.com)  
 Internet: [www.hydac.com](http://www.hydac.com)